
DATA SHEET



25" ACTIVESMART™ FRIDGE - BOTTOM FREEZER

Model no:

RF135BDRUX4 (refer page 1 for metric measurements)

Product Dimensions	ir
Overall height* of fridge	67 1/2
Overall width of fridge	25'
© Depth of fridge door and gasket (excludes handle)	2 3/4
Depth of fridge door and chassis (excludes handle)	27 3/8'
Depth of fridge chassis (does not include fridge door)	24 5/8
Height from bottom datum to top of fridge door	66 9/16
Height of feet (adjustable)	15/16'
Height from bottom datum to bottom of bottom door	5/8'
Height from bottom datum to bottom of bottom handle	9 5/8
Height from bottom datum to top of bottom handle	24 3/8
Height from bottom datum to top of bottom door	24 3/4
© Height from bottom datum to bottom of top door	25 1/8'
Height from bottom datum to bottom of top handle	25 1/2
Height from bottom datum to top of top handle	49 9/16'
Width of handle	5/8'
Depth of handle (measured from front of door)	1 5/8'
Depth of door (open at 90°) (measured from front of door)	29 1/4'
Rotation of door (open) (measured from front of door)	138
* Includes mounted feet	

^{*} Includes mounted feet

Minimum Clearances	in
Minimum height of cavity	68 5/16"
Minimum side clearance installed flush with chassis	13/16"
Side clearance (hinge side) – installed flush with door - full rotation	5 5/16"
Rear clearance (including evaporator tray)	1 3/16"


INDICATES PRODUCT DATUM -----INDICATES CABINETRY CLEARANCES ------

DATE: 2.12.2015

IMPORTANT NOTE: Throughout this guide, dimensions may vary by $\pm 2 \text{mm}$ (3/32"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com



DATA SHEET



635MM ACTIVESMART™ FRIDGE - BOTTOM FREEZER

Model no:

RF135BDRUX4 (refer page 2 for imperial measurements)

Product Dimensions	mn
Overall height* of fridge	171
Overall width of fridge	63
© Depth of fridge door and gasket (excludes handle)	70
Depth of fridge door and chassis (excludes handle)	69
© Depth of fridge chassis (does not include fridge door)	62
E Height from bottom datum to top of fridge door	169
Height of feet (adjustable)	24
Height from bottom datum to bottom of bottom door	1
① Height from bottom datum to bottom of bottom handle	240
Height from bottom datum to top of bottom handle	619
Height from bottom datum to top of bottom door	629
Height from bottom datum to bottom of top door	639
Height from bottom datum to bottom of top handle	648
Height from bottom datum to top of top handle	1260
Width of handle	1:
Depth of handle (measured from front of door)	4
Depth of door (open at 90°) (measured from front of door)	59
Rotation of door (open) (measured from front of door)	138

 Minimum Clearances
 mm

 Minimum height of cavity
 1735

 Minimum side clearance installed flush with chassis
 20

 Side clearance (hinge side) – installed flush with door - full
 135

rotation
Rear clearance (including evaporator tray)
30

INDICATES PRODUCT DATUM -----INDICATES CABINETRY CLEARANCES ------

DATE: 2.12.2015

IMPORTANT NOTE: Throughout this guide, dimensions may vary by $\pm 2 \text{mm}$ (3/32"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com

